

# LogiLink®



## USB-C™ 2-Port Wall Charger, 18 W

1x USB-C™ PD Port & 1x QC USB Port

Art. No.: PA0220

Portable designed for fast charging dual devices simultaneously,  
perfect for traveling.



Best Connectivity



RoHS  
compliant



\*The specifications and pictures are subject to change without prior notice.  
\*All trade names referenced are the registered trademarks of their respective owners.



PA0220



4 052792 057089

Made in China

# LogiLink®

## USB-C™ 2-Port Wall Charger, 18 W

1x USB-C™ PD Port & 1x QC USB Port

Art. No.: PA0220



### Rapid Charging with PD3.0 and QC3.0

Charge your power-hungry devices with one USB-C PD port and one USB-A fast charging port.



### Multiple Protection

Supports overcurrent, overvoltage, overheating and short circuit protections.



\*The specifications and pictures are subject to change without prior notice.  
\*All trade names referenced are the registered trademarks of their respective owners.



Made in China

Best Connectivity

# LogiLink®

## USB-C™ 2-Port Wall Charger, 18 W

1x USB-C™ PD Port & 1x QC USB Port

Art. No.: PA0220



### Wide Compatibility

Compatible with most mobile devices: smartphones, tablets and much more.



### Travel-Ready

Compact size easily fit in to laptop bag or backpack.

Best Connectivity



RoHS  
compliant



\*The specifications and pictures are subject to change without prior notice.  
\*All trade names referenced are the registered trademarks of their respective owners.



PA0220



Made in China



# LogiLink®



## USB-C™ 2-Port Wall Charger, 18 W

1x USB-C™ PD Port & 1x QC USB Port

Art. No.: PA0220

### Specification:

Input	100–240 V AC 50/60 Hz 1A max.
Output	USB-A port: 5 V/3 A (15 W), 9 V/2 A (18 W), 12 V/1.5 A (18 W) USB-C port: 5 V/3 A (15 W), 9 V/2 A (18 W), 12 V/1.5 A (18 W) <i>*Max. Total Output 18 W</i>
Protections	Overcurrent, overvoltage, overheating and short circuit
Efficiency	Level V
Operating Temperature Range	0–40°C
Storage Temperature Range	-40°C–85°C
Relative Humidity	25%–90% (non-condensing)
Storage Humidity	10%–90% (non-condensing)
Dimension	89x51x29 mm
Weight	62 g



### Package Contents:

- » 1x USB Wall Charger
- » 1x User Manual

### Package Information:

- » Packing Dimension: 138x75x45 mm
- » Packing Weight: 0.107 kg
- » Carton Dimension: 465x315x167 mm
- » Carton Q'ty: 40 pcs
- » Carton Weight: 4.98 kg



⚠ Proper use of the PD function can only be guaranteed in combination with certified USB cables with E-Mark chipset.

\*The specifications and pictures are subject to change without prior notice.  
\*All trade names referenced are the registered trademarks of their respective owners.



Made in China

Best Connectivity