



LogiLink®

Mobile Power Bank


10000 mAh

Art. No.: PA0275

Stay Powered, Stay Connected

The high capacity power bank is powerful enough to charge your smart devices with a push of a button. Slim and compact design for easy charge on-the-go.


Power
Charge



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.

10000mAh



Power on the Go

The 10000 mAh capacity provides multiple charges for your mobile devices wherever you are.


Convenient Simultaneous Charging

Fast charging of two devices with USB-C PD 2.0 and USB-A QC 3.0 ports at the same time; delivers up to 18 W for your power hungry devices.



Fast Charging Inputs

Quickly charge your power bank with the USB-C or Micro-B port.



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.

2 in 1 USB-C & Micro-B cable included



Wide Compatibility

Compatible with any USB-enabled device such as smartphones, smartwatches, tablets, headphones, digital cameras and much more.



Pocket-Sized Portability

Lightweight and slim design, easily slips into your pocket or bag. Take it with you wherever you go.



Multiple Protection

Extremely safe and reliable, these power banks come with overcurrent, overvoltage, overheating and short circuit protection.



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.

Made in China

Specifications:

Battery Capacity	10000 mAh
Battery Cell	3,7 V lithium battery
Input Power (Max.)	Micro USB : 5 V/2 A. 9 V/2 A. 12 V/1,5 A (18 W) USB-C: 5 V/3 A. 9 V/ 2 A. 12 V/1,5 A (18 W) *Total input 18 W max.
Power Input Interface	USB-C & Micro-B
Output Power (Max.)	USB-A :5 V/3 A. 9 V/ 2 A. 12 V/1,5 A (18 W) USB-C :5 V/3 A. 9 V/ 2 A. 12 V/1,5 A (18 W) *Total output 18 W max.
Power Output Interface:	USB-C & USB-A
Housing Material	ABS
LED Indicator	White LED for charging and power indicator
Dimension (mm)	13,8x6,8x1,7 cm
Weight (g)	232 g
Smart Fast Charging	Yes
Quick Charging	QC 3.0
Power Delivery	PD 2.0
Charging Cable Type	2-in-1 USB-C & Micro-B charging cable
Cable Length (cm)	30 cm
Operating Temperature	-10–45°C
Operating Humidity	40–60% RH (no condensation)
Storage Temperature	0–40°C
Storage Humidity	40–60% RH (no condensation)

Package Contents:

- » 1x 10000 mAh Power Bank
- » 1x 2 in 1 USB-C & Micro-B Cable
- » 1x User Manual

Package Information:

- » Packing Dimension: 175x90x25 mm
- » Packing Weight: 0,267 kg
- » Carton Dimension: 380x270x190 mm
- » Carton Q'ty: 40 pcs
- » Carton Weight: 11,5 kg



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.



Made in China