



Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 26.06.2018

Version number 3

Revision: 26.06.2018

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1 Product identifier**

Item no. 630474000 / Hedge trimmer maintenance oil 1

Article number: 17091000, 17 2200

1.2 Relevant identified uses of the substance or mixture and uses advised against
No further relevant information available.

Application of the substance / the mixture: Lubricating oil

1.3 Details of the supplier of the safety data sheet**Company: Metabowerke GmbH - Metabo-Allee-1, DE-72622 Nürtingen****Phone: 0049 / (0) 7022 - 720**

Further information obtainable from: Product safety department

1.4 Emergency telephone number: During normal opening times: +49 7762 800-734

SECTION 2: Hazards identification**2.1 Classification of the substance or mixture**

Classification according to Regulation (EC) No 1272/2008

The product is not classified, according to the CLP regulation.

2.2 Label elements

Labelling according to Regulation (EC) No 1272/2008 Void

Hazard pictograms Void

Signal word Void

Hazard statements Void

2.3 Other hazards

Results of PBT and vPvB assessment

PBT: Not applicable.

vPvB: Not applicable.

SECTION 3: Composition/information on ingredients**3.2 Chemical characterisation: Mixtures**

Description: Mixture of substances listed below with nonhazardous additions.

Dangerous components: Void

Additional information: For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures**4.1 Description of first aid measures**

General information: No special measures required.

After skin contact: Generally the product does not irritate the skin.

After eye contact: Rinse opened eye for several minutes under running water.

After swallowing: If symptoms persist consult doctor.

4.2 Most important symptoms and effects, both acute and delayed No further relevant information available.

(Contd. on page 2)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 26.06.2018

Version number 3

Revision: 26.06.2018

Item no. 630474000 / Hedge trimmer maintenance oil 1

(Contd. of page 1)

- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:** Use fire extinguishing methods suitable to surrounding conditions.
- **5.2 Special hazards arising from the substance or mixture** No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:** No special measures required.
- **Additional information**
Collect contaminated fire fighting water separately. It must not enter the sewage system.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** No special measures required.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** None.
- **Storage class:** 10
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **8.1 Control parameters**
- **Ingredients with limit values that require monitoring at the workplace:**
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
The usual precautionary measures are to be adhered to when handling chemicals.
- **Respiratory protection:** Not necessary if room is well-ventilated.
- **Protection of hands:**
The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

(Contd. on page 3)

EU

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 26.06.2018

Version number 3

Revision: 26.06.2018

Item no. 630474000 / Hedge trimmer maintenance oil 1

(Contd. of page 2)

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **For the permanent contact gloves made of the following materials are suitable:** Nitrile rubber, NBR

· **Eye protection:** Goggles recommended during refilling

SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

· Form:	Fluid
· Colour:	Brown
· Odour:	Characteristic
· Odour threshold:	Not determined.

· **pH-value:** Not determined.

· **Change in condition**

· Melting point/freezing point:	Undetermined.
· Initial boiling point and boiling range:	201 °C

· **Flash point:** 121 °C

· **Flammability (solid, gas):** Not applicable.

· **Ignition temperature:** 200 °C

· **Decomposition temperature:** Not determined.

· **Auto-ignition temperature:** Product is not selfigniting.

· **Explosive properties:** Product does not present an explosion hazard.

· **Explosion limits:**

· Lower:	Not determined.
· Upper:	Not determined.

· **Vapour pressure:** Not determined.

· **Density at 20 °C:** 0.89 g/cm³

· **Relative density** Not determined.

· **Vapour density** Not determined.

· **Evaporation rate** Not determined.

· **Solubility in / Miscibility with water:**

Not miscible or difficult to mix.

· **Partition coefficient: n-octanol/water:** Not determined.

· **Viscosity:**

· Dynamic:	Not determined.
· Kinematic:	Not determined.

(Contd. on page 4)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 26.06.2018

Version number 3

Revision: 26.06.2018

Item no. 630474000 / Hedge trimmer maintenance oil 1

(Contd. of page 3)

- **Solvent content:**
- VOC (EC)** 0.00 %
- **9.2 Other information** No further relevant information available.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.
- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation** Smaller quantities can be disposed of with household waste.

(Contd. on page 5)

EU

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 26.06.2018

Version number 3

Revision: 26.06.2018

Item no. 630474000 / Hedge trimmer maintenance oil 1

(Contd. of page 4)

· **European waste catalogue**

13 02 07*	readily biodegradable engine, gear and lubricating oils
15 01 04	metallic packaging

· **Uncleaned packaging:**· **Recommendation:** Disposal must be made according to official regulations.**SECTION 14: Transport information**· **14.1 UN-Number**· **ADR, ADN, IMDG, IATA** Void· **14.2 UN proper shipping name**· **ADR, ADN, IMDG, IATA** Void· **14.3 Transport hazard class(es)**· **ADR, ADN, IMDG, IATA**· **Class** Void· **14.4 Packing group**· **ADR, IMDG, IATA** Void· **14.5 Environmental hazards:**· **Marine pollutant:** No· **14.6 Special precautions for user** Not applicable.· **14.7 Transport in bulk according to Annex II of Marpol and the IBC Code** Not applicable.· **UN "Model Regulation":** Void**SECTION 15: Regulatory information**· **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**· **Directive 2012/18/EU**· **Named dangerous substances - ANNEX I** None of the ingredients is listed.· **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.**SECTION 16: Other information**

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Department issuing SDS:** Product safety department· **Contact:** Mr. Weber, PhD.· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU)

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative