

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5013311107

Status:

Active

Overview:

Pico-Clasp Wire-to-Board Connectors

Description:

1.00mm Pitch, Pico-Clasp PCB Header, Single Row, Vertical, Surface Mount, Tin Plated, Inner Positive Lock, 11 Circuits, Natural

Documents:

- 3D Model (PDF)

3D Model

Drawing (PDF)

Product Specification 5013300000-PS-001 (PDF)

Product Specification 5013301000-PS-001 (PDF)
- Application Specification 5013300000-AS-000 (PDF)

Packaging Specification SPK-501331-001-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Component Type

Overview

Product Name

Taxonomy

UPC

PCB Headers

501331

Signal, Wire-to-Board

PCB Header

Pico-Clasp Wire-to-Board Connectors

Pico-Clasp

PCB Headers and Receptacles

822348542826

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Glow-Wire Capable

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Retention

Packaging Type

Pitch - Mating Interface

Polarized to Mating Part

Polarized to PCB

Robotic Placement

Shrouded

Stackable

Temperature Range - Operating

Termination Interface: Style

No

11

11

Natural

30

No

No

Yes

Phosphor Bronze

Tin

Tin

Nylon

224.200/mg

1

Vertical

No

Yes

Embossed Tape on Reel

1.00mm

Yes

No

Vacuum Pick-Up Tape

Fully

No

-40° to +105°C

Surface Mount

Electrical

Current - Maximum per Contact

Voltage - Maximum

1.0A

100V AC (RMS)/DC



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

501331 Series

Mates With

501330 Pico-Clasp Wire-to-Board Female Housing

Material Info

Reference - Drawing Numbers

Application Specification	5013300000-AS-000
Packaging Specification	SPK-501331-001-001
Product Specification	5013300000-PS-001, 5013301000-PS-001
Sales Drawing	5013310000-SD-000, 5013310612-SD-000

This document was generated on 01/25/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION