

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0347928080

Status:


Active

Overview:

Mini50 Connection Systems

Description:

Mini50 Unsealed Vertical Header, Single Row, 8 Circuit, Polarization Option A, Black, Tape and Reel



Series image - Reference only

- Documents:
- 3D Model

Application Specification AS-34791-020-CH-001 (PDF)
- Drawing (PDF)

Test Summary 347910020-TS-000 (PDF)
- 3D Model (PDF)

Datasheet (PDF)
- Product Specification PS-34791-020-001 (PDF)

RoHS Certificate of Compliance (PDF)
- Application Specification AS-34791-020-001 (PDF)

General	
Product Family	PCB Headers
Series	34792
Application	Automotive, Power, Signal, Wire-to-Board
Component Type	PCB Header
Overview	Mini50 Connection Systems
Product Name	Mini50
Taxonomy	PCB Headers and Receptacles
UPC	889056918718

Physical	
Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester Alloy
Net Weight	1.541/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	2.90mm
PCB Locator	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical	
Current - Maximum per Contact	4.0A (for reference only)
Voltage - Maximum	14V (typical operating)

Material Info

Reference - Drawing Numbers	
Application Specification	AS-34791-020-001, AS-34791-020-CH-001

EU ELV
Compliant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free
Status
Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
34792 Series

Mates With
34791 Mini50 Unsealed Single Row
Receptacle

Product Specification
Sales Drawing
Test Summary

PS-34791-020-001
SD-34792-001-001
347910020-TS-000

This document was generated on 02/06/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION