

Crimp connector assortment 500 pcs set



Fork connectors, ring terminals, blade receptacles, flat plugs, round plugs, round plug sleeves

Item No. 22C424



Quadrios crimp connectors guarantee optimal results in conjunction with fitting crimping tools. This product series includes the most common parts used in practice. The assortment is especially suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs.

Content	Description	Material	Cross section
25 pcs	Fork connector red, holeØ 3.1 mm	Copper, tin plated	0.5...1.5 mm ²
25 pcs	Fork connector blue, holeØ 4.1 mm	Copper, tin plated	0.5...1.5 mm ²
20 pcs	Fork connector red, holeØ 5.2 mm	Copper, tin plated	1.5...2.5 mm ²
25 pcs	Ring terminal red, holeØ 3.1 mm	Copper, tin plated	0.5...1.5 mm ²
25 pcs	Ring terminal blue, holeØ 4.1 mm	Copper, tin plated	0.5...1.5 mm ²
20 pcs	Ring terminal red, holeØ 5.2 mm	Copper, tin plated	1.5...2.5 mm ²
25 pcs	Fork connector red, holeØ 3.1 mm	Copper, tin plated	0.5...1.5 mm ²
25 pcs	Fork connector blue, holeØ 4.1 mm	Copper, tin plated	0.5...1.5 mm ²
20 pcs	Fork connector red, holeØ 5.2 mm	Copper, tin plated	1.5...2.5 mm ²
25 pcs	Ring terminal red, holeØ 3.1 mm	Copper, tin plated	0.5...1.5 mm ²
25 pcs	Ring terminal blue, holeØ 4.1 mm	Copper, tin plated	0.5...1.5 mm ²
20 pcs	Ring terminal red, holeØ 5.2 mm	Copper, tin plated	1.5...2.5 mm ²
25 pcs	Blade receptacles red, 2.8 mm	Copper, tin plated	0.5...1.5 mm ²
25 pcs	Blade receptacles blue, 4.8 mm	Copper, tin plated	0.5...1.5 mm ²
20 pcs	Blade receptacles yellow, 6.3 mm	Copper, tin plated	1.5...2.5 mm ²
25 pcs	Flat plug red, 2.8 mm	Copper, tin plated	0.5...1.5 mm ²
25 pcs	Flat plug blue, 4.8 mm	Copper, tin plated	0.5...1.5 mm ²
20 pcs	Flat plug yellow, 6.3 mm	Copper, tin plated	1.5...2.5 mm ²
20 pcs	Round plug red, Ø 4 mm	Copper, tin plated	0.5...1.5 mm ²
20 pcs	Round plug sleeve red, Ø 4 mm	Copper, tin plated	1.5...2.5 mm ²
20 pcs	Round plug blue, Ø 4 mm	Copper, tin plated	0.5...1.5 mm ²
20 pcs	Round plug sleeve blue, Ø 4 mm	Copper, tin plated	1.5...2.5 mm ²

Connection only by qualified electricians!