

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191640306

Status:


Active

Overview:

Perma-Seal Terminals

Description:

Perma-Seal Ring Tongue Terminal for 18-22 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier



Documents:

Drawing (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-015-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19164
Crimp Quality Equipment	Yes
Overview	Perma-Seal Terminals
Product Name	Perma-Seal
Taxonomy	Ring and Spade Terminals
Type	Ring
UPC	800753115613
Physical	
Barrel Type	Closed
Insulation	NiAc
Material - Plating Mating	Tin
Net Weight	0.597/g
Packaging Type	Adhesive Tape on Reel
Stud Size	10 (M5)
Wire Insulation Diameter	5.97mm
Wire Size AWG	18, 20, 22
Wire Size mm²	0.38-0.96
Material Info	
Engineering Number	SA-221-10T
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-015-001
Sales Drawing	SD-19164-006-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2022)4187-DC (10

June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19164 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
ATP Perishable	198082009
Tool Kit used in ATP	
Presses that Process	
18-22 AWG Product	
on Tape	
PremiumGrade	640017400
Hand Crimp Tool for	
Industrial Terminals,	
10-22 AWG (see	
ATS)	
Power Crimp Tool	640057400
Head for Terminals	
10-22 AWG Wire	

ServiceGrade Hand 640160041
Crimp Tool for Field
Repair only, for
production use our
PremiumGrade Tool

This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION