

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1111451101

Status:

Active

Overview:

zSFP+ Interconnect System

Description:

zSFP+-to-zSFP+ Passive Cable Assembly, 28 Gbps, 30 AWG, 1.0m Length



Series image - Reference only

Documents:

Drawing (PDF)	Test Summary 1111451201-001 (PDF)
Packaging Specification 1111451000-000 (PDF)	Test Summary 1111451201-002 (PDF)
Test Summary 1111451051-000 (PDF)	Test Summary 1111451201-003 (PDF)
Test Summary 1111451101-SI (PDF)	Test Summary 1111451201-005 (PDF)
Test Summary 1111451151-002 (PDF)	Test Summary 1111451201-006 (PDF)
Test Summary 1111451151-005 (PDF)	Test Summary 1111451201-009 (PDF)
Test Summary 1111451151-006 (PDF)	Datasheet (PDF)
Test Summary 1111451151-007 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Cable Assemblies
Series	111145
Assembly Configuration	Dual Ended Connectors
Comments	Delivering unparalleled signal integrity for next-generation Ethernet and Fibre Channel applications, the zSFP+ cable assemblies for 28 Gbps serial channels now includes Temp-Flex cable technology.
Connector to Connector	SFP28-to-SFP28, zSFP+-to-zSFP+
Overview	zSFP+ Interconnect System
Product Name	zSFP Plus, zSFP+
Taxonomy	High-Speed Pluggable I/O Cable
UPC	889056483148

Physical

Cable Length	1.0m
Circuits (Loaded)	20
Gender	Plug/Plug
Lock to Mating Part	Yes
Material - Metal	Zinc Die Cast
Material - Plating Mating	Gold
Net Weight	72.000/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	0.80mm
Single Ended	No
Waterproof / Dustproof	No
Wire Insulation Diameter	4.10mm Nominal
Wire Size AWG	30
Wire/Cable Type	Temp-Flex Twinax

Electrical

Current - Maximum per Contact	0.03A
Impedance	100Ω
Shield Type	EMI Girdle
Shielded	Yes
Voltage - Maximum	3.3V DC

Material Info

Reference - Drawing Numbers

Packaging Specification	1111451000-000
Sales Drawing	1111450001-000

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

111145 Series

Mates With

zSFP+ Connectors [170382](#)

Use With

Switches, hubs, routers, servers, storage,
telecom

1111451051-000, 1111451101-SI, 1111451151-002,
1111451151-005, 1111451151-006, 1111451151-007,
1111451201-001, 1111451201-002, 1111451201-003,
1111451201-005, 1111451201-006, 1111451201-009

This document was generated on 01/16/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION