

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0369240301

Status:

Active

Overview:

Description:

Mini-Fit Sr.-to-Mini-Fit Sr. Off-the-Shelf (OTS) Cable Assembly, 10.00mm Pitch, Single Row, 0.15m Length, 3 Circuits, Black

General	
Product Family	Cable Assemblies
Series	36924
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Comments	Terminal Position Assurance (TPA) Clip Included
Connector to Connector	Mini-Fit Sr.-to-Mini-Fit Sr.
Overmolded	No
Overview	minifit_sr
Product Name	Mini-Fit Sr.
Taxonomy	Power and Signal Cable Assembl
Type	Discrete Wire Assembly, High-Power Assembly
UPC	193264249749

Physical	
Cable Length	0.15m
Circuits (Loaded)	3
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	78.127/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	10.00mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	6.60mm max.
Wire Size AWG	8
Wire/Cable Type	UL 1015

Electrical	
Current - Maximum per Contact	50.0A
Voltage - Maximum	600V AC/DC

Material Info

Reference - Drawing Numbers	
Sales Drawing	369240300-000

EU ELV
Not Relevant

EU RoHS
Compliant
REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free
Status

Not Low-Halogen
For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
36924 Series

Mates With
Mini-Fit Sr. Plug Housing [428180312](#) .
Mini-Fit Sr. Vertical Header [428193213](#)
, [428193223](#) , [428193233](#) , [428193243](#) .
Mini-Fit Sr. Right-Angle Header [428203213](#)
, [428203223](#) , [428203228](#) , [428203233](#) ,
[428203243](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION