

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0348406410

Status:


Active

Overview:

MX150 Connector System

Description:

MX150 Male Connector Assembly, Bulkhead Twist-Lock, Mat-Sealed Compatible, Dual Row, 12 Circuits, Keying Option A, Black



|                                               |                                                  |
|-----------------------------------------------|--------------------------------------------------|
| Documents:                                    |                                                  |
| 3D Model                                      | Application Specification AS-34840-001-001 (PDF) |
| 3D Model (PDF)                                | Packaging Specification PK-31301-615-001 (PDF)   |
| Drawing (PDF)                                 | Datasheet (PDF)                                  |
| Product Specification PS-34840-0001-001 (PDF) | RoHS Certificate of Compliance (PDF)             |

|                               |                            |
|-------------------------------|----------------------------|
| General                       |                            |
| Product Family                | Crimp Housings             |
| Series                        | 34840                      |
| Application                   | Power, Wire-to-Wire        |
| Overview                      | MX150 Connector System     |
| Product Name                  | MX150                      |
| Taxonomy                      | Connector Housings         |
| UPC                           | 191128256759               |
| Physical                      |                            |
| Circuits (maximum)            | 12                         |
| Color - Resin                 | Black, Natural             |
| Gender                        | Plug                       |
| Glow-Wire Capable             | No                         |
| Keying to Mating Part         | Yes                        |
| Lock to Mating Part           | Yes                        |
| Material - Resin              | Modified Polystyrene Alloy |
| Net Weight                    | 24.020/g                   |
| Number of Rows                | 2                          |
| Packaging Type                | Bag                        |
| Panel Mount                   | Yes                        |
| Pitch - Mating Interface      | 3.50mm                     |
| Polarized to Mating Part      | Yes                        |
| Stackable                     | No                         |
| Temperature Range - Operating | -40° to +125°C             |
| Material Info                 |                            |
| Reference - Drawing Numbers   |                            |
| Application Specification     | AS-34840-001-001           |
| Packaging Specification       | PK-31301-615-001           |
| Product Specification         | PS-34840-0001-001          |
| Sales Drawing                 | SD-34840-001-001           |

|                                                                       |                                           |
|-----------------------------------------------------------------------|-------------------------------------------|
| EU ELV<br>Compliant                                                   |                                           |
| EU RoHS<br>Compliant                                                  | China RoHS                                |
| REACH SVHC<br>Not Contained Per -<br>D(2022)4187-DC (10<br>June 2022) |                                           |
| Halogen-Free<br>Status<br>Low-Halogen                                 |                                           |
| For more information, please visit <a href="#">Contact US</a>         |                                           |
| China ROHS<br>ELV<br>RoHS Phthalates                                  | Green Image<br>Compliant<br>Not Contained |

|                                             |
|---------------------------------------------|
| Search Parts in this Series<br>34840 Series |
| Mates With<br>33472 MX150 Sealed Connector  |
| Use With<br>33000 MX150 Male Terminal       |

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION