

## Ferrule assortment 1200 pcs (DIN color code) Bundle-Type: 22T023

These ferrules are especially suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs.

The assortment contains a 1200-piece premium ferrule set (DIN color code) for an application range of cable cross sections from 0.5 to 10 qmm. Optimal for use with suitable wire end ferrule crimping pliers.



### Technical Specifications

Voltage (max.): 440 V, Material: polyamide, copper alloy. The ferrules comply with RoHS directives and are CE compliant. Further technical data on the included components are noted in the data sheet. Installation by qualified electricians only.

### Content

Practical assortment box, 25 ferrules yellow 6 qmm (10 AWG), 25 ferrules red 10 qmm (7 AWG), 50 ferrules grey 4 qmm (12 AWG), 250 ferrules blue 2,5 qmm (14 AWG), 250 ferrules black 1.5 qmm (16 AWG), 200 ferrules gray 0.75 qmm (20 AWG), 200 ferrules red 1 qmm (18 AWG), 200 ferrules white 0.5 qmm (22 AWG).

## Self Adjusting Wire-End Ferrule Crimping Pliers Range 0.25...10 mm<sup>2</sup> Bundle-Type.: 22T023




This crimping tool is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs. The crimping tool is optimally matched to the field of application and has an automatic adjustment to the sleeve diameters between 0.25 and 10 qmm. The square crimping claw ensures a safe crimping process, the ergonomic handle fits well in the hand and allows comfortable working. The pliers have an adjustment option for fine adjustment of the compressive force and a quick locking safety lock.



### Technical Specifications

Four-mandrel press claw • Automatic adjustment • Fine adjustment ratchet pressure • Quick release safety lock • ergonomic handle • Range from 0.25 to 10 mm<sup>2</sup>.

### Usage example



Application by qualified electricians only.

Works best with Quadrios` ferrule assortment sets.



## Automatic multifunction wire stripper Bundle-Type.: 22T023



This automatic multifunction wire stripper is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs. The tool provides a lot of helpful functions and is made of high quality materials.

### Technical Specifications

Size: 210 x 108 mm • Material: carbon steel S50C, handle PP/TPR • Stripping function for cable, cross section: 10 ... 24 AWG / 0.25 ... 5.2 mm<sup>2</sup> • Wire cutter function for copper and aluminum wires • Crimping function for ferrules (insulated/uninsulated) 10 ... 22 AWG / 0.35 ... 5.2 mm<sup>2</sup> • Crimp function for ignition terminals 7 / 8 mm<sup>2</sup>.

Application by qualified electricians only.