



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Locking & Mounting



D-Shaped Connector Accessories: **Slide Latch Kit**

Screw Length: **10.54 mm [.415 in]**

Features

Product Type Features

Product Type	Accessory
Latch Type	Slide Latch
D-Shaped Connector Accessories	Slide Latch Kit

Body Features

Latch Material	Stainless Steel
----------------	-----------------

Mechanical Attachment

Screw Plating Material	Zinc
Screw Material	Steel
Screw Finish	Yellow Chromate
Screw & Hole Thread Size	4-40
Screw Length	10.54 mm[.415 in]

Operation/Application

For Use With	Connectors With Cable Clamp Housings
--------------	--------------------------------------

Packaging Features

Packaging Quantity	1
Packaging Method	Kit



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (.35% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | **AMPLIMITE Kit**



D-Sub Backshells & Clamps(135)



D-Sub Contact Accessories(1)



D-Sub Covers(3)




D-Sub Locking & Mounting(120)

Customers Also Bought




TE Part #1658608-1
37 POS HDF PLUG, MS, LEAD FREE



TE Part #1734715-2
RJ45,MULTI-PORT,2x4,T/H,SHEILDED.



TE Part #1546670-5
5P .437" DR BARRIER,W/BND SCRW



TE Part #1-87456-0
14 MODIV HSG DR MRKD .100CL



TE Part #5-2176341-7
CRGCQ 0805 470K 1%



TE Part #5748676-5
DIE CAST CBL CLMP KIT,SZ 5



TE Part #2-320571-5
TERMINAL,PIDG R IR 18 1/4



TE Part #YDTS20F15-19SNV001
RECP ASSY



TE Part #31679
TERMINAL,DG R 26-22 4



TE Part #770253-4
UMNL II SOK SNAUNIPHBZ LP24-18

Documents

Product Drawings
SLIDELATCH KIT, 50 POS
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_5745578-3_O.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_5745578-3_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5745578-3_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - Cable Connectors](#)

English

[AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English