

LogiLink®

Vlogger Starter Kit

With LED Light, Microphone and Tripod

Art. No.: AA0157



Vlogging Kit



Selfie



Level Up Your Vlog's Video Quality

The Vlogger Starter Kit includes a 2-in-1 mini tripod, can be handheld or place on desktop; a cardioid unidirectional microphone with foam windscreen and a LED light with 3 brightness levels. Featuring universal 1/4" screw works for smartphones or cameras, perfect for blogging, recording, filmmaking or live-streaming.



For 4.7-7"
Smartphone



Adjustable
Brightness



Shotgun
Microphone



110°
Tripod
Tilting Angle



3.5mm Audio
Connection

Ultra Bright 3 Levels LED

Features cold shoe mounts to install the microphone, and 1/4" screw to lock on phone holder or camera.



Crisp & Clear Sound

Unidirectional cardioid shotgun microphone with foam windscreen.

3.5 mm TRS audio connection

Compatible with 4.7-7" smartphones and cameras

110° tilt angle


Easy-to-grip handle



Quick setup for professional filming

Recording Stability

Take videos or selfie with mini tripod, or handheld on the go, always be sure to record in stable conditions.



Specifications:

Microphone	
Polar Pattern	Cardioid
Sample Rate	48 kHz
Bit Rate	16 bit max.
Impedance	Max. 0.68 k Ω 1 kHz (RL=0.68 k Ω)
Frequency Range	50 Hz–16 kHz
SNR	>66 dB
Equivalent Noise	24 dB
Maximum SPL	115 dB
Sensitivity	-39 \pm 1 dB RL=0.68 K Ω Vs=1.5 V (1 kHz 0 dB=1 V/Pa)
Power Supply	Via smartphone (2–5 V DC)
Microphone Output	3.5 mm TRS mini jack (single mono)
Cable Length	0.3 m
Housing Material	ABS
Dimensions	8.6 x 5.7 x 2.95 cm
Weight	26 g
LED Light	
LED Type/Quantity	SMD 2835 LED 0.2 W/36 pcs
Total Luminous Flux	130 lm
Color Temperature Mode	Cool color
Brightness Levels	3 levels
Correlated Color Temperature	6500 K
Power By	2x 1.5 V AA alkaline battery (not included)
On/Off Switch	Yes
Dimensions	7.83 x 6.6 x 3.27 cm
Weight	52 g
Smartphone Holder and Tripod	
Fit to Smartphone Size	65–105 mm
Tripod Tilt Angle	110°
Connection Screw	1/4", 6 mm
Dimensions	Smartphone holder: 8.1 x 3 x 2.6 cm Tripod: 13.8 x 9.4 x 3.48 cm
Weight	126 g
Operating Temperature	-10–65°C
Operating Humidity	30–85% RH (non-condensing)

Package Contents:

- » 1x Tripod
- » 1x LED Light
- » 1x Smartphone Holder
- » 1x Microphone
- » 1x AUX Cable
- » 1x User Manual

Package Information:

- » Packing Dimension: 208 x 173 x 45 mm
- » Packing Weight: 0.306 kg
- » Carton Dimension: 480 x 432 x 365 mm
- » Carton Q'ty: 40 pcs
- » Carton Weight: 12.85 kg



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.



AA0157



Made in China