

LogiLink®



Industrial Fast Ethernet Switch, 5-Port

Art. No.: NS200

Compact size 5-Port 10/100 Base-TX Ethernet Switch, suitable for industrial application. Featuring 5 10/100 Mbps auto-negotiation RJ45 ports, IP40-rated rugged aluminum case and a wide-ranging redundant power system (12–52 V DC). It is able to operate in any harsh environment with operating temperature ranging from -40 to 80°C.

Features:

- » Industrial switch, 5-port, 10/100Base-TX RJ45
- » Unmanaged, easy installation, plug-and-play
- » Compact and rugged metal housing, IP40
- » Free fall, shock and vibration stability
- » Power input: 12 to 52 V DC redundant power
- » Extended operation temperature: -40–80°C
- » Suitable for DIN-rail mounting



Specification:

Protocols/Standards	IEEE 802.3, IEEE 802.3i, IEEE 802.3u, IEEE 802.3x
Interface	5 x 10/100 Mbps RJ45 ports
Bandwidth	1,6 Gbps
Packet Buffer Memory	1 Mbit
Packet Forwarding Rate	1,2 Mpps
MAC Address Table	2K
Maximum Frame Size	9K bytes packet size
Flow Control	Back pressure for half duplex, IEEE 802.3x pause frame for full duplex
LED Indicator	Power: Red; Ethernet: Yellow
Network Cables	10Base-T: Cat.3/4/5 UTP (≤100 m); 100Base-TX: Cat.5 or later UTP (≤100 m)
Power Input	12–52 V DC redundant power
Power Consumption	Max. 3 W
Surge Protection	±4 KV



NS200



4 052792 067323

Made in China



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.

Best Connectivity


LogiLink®



Industrial Fast Ethernet Switch, 5-Port

Art. No.: NS200

Installation	DIN rail
Enclosure	IP40 aluminum housing
MTBF	>300.000 hours
Operating Temperature	-40–80°C
Storage Temperature	-40–80°C
Storage Humidity	5–95% RH non-condensing
Dimension	11,8 x 8,6 x 3,35 cm
Weight	0,36 kg



Package Contents:

- » 1 x 5-Port Fast Ethernet Switch
- » 1 x User Manual

Package Information:

- » Packing Dimension: 165 x 135 x 54 mm
- » Packing Weight: 0,41 kg
- » Carton Dimension: 445 x 350 x 343 mm
- » Carton Q'ty: 36 pcs
- » Carton Weight: 15,5 kg



NS200



4 052792 067323

Made in China



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.

Best Connectivity