

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0433750001

Status:

Active

Overview:

Sabre Power Connector

Description:

Sabre Single Crimp Terminal, Female, 14-16 AWG, 3.30mm Max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact with TPA

Documents:

Drawing (PDF)

Product Specification PS-44441-9999-001 (PDF)

Packaging Specification 433750000-PK-000 (PDF)

Test Summary 444410000-TS-000 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	43375
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Terminal mates to 3.18mm wide x 0.51mm thick flat blade PC tab. Allows 44441 receptacle housings to comply with the UL1977 finger proof access requirement
Crimp Quality Equipment	Yes
Overview	Sabre Power Connector
Product Name	Sabre
Taxonomy	Crimp Terminals
UPC	800754365970
Physical	
Durability (mating cycles max)	25
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	425.000/mg
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.30mm max.
Wire Size AWG	14, 16
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	18.0A
Voltage - Maximum	600V
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	433750000-PK-000
Product Specification	PS-44441-9999-001
Sales Drawing	SD-43375-0001-001
Test Summary	444410000-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Not Relevant

Status

Low-Halogen

For more information, please visit

Contact US

Search Parts in this Series

43375 Series

Use With

44441 Receptacle Housings

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
PremiumGrade Hand	638117200
Crimp Tool for Sabre	
Terminals, 14-18	
AWG	
Extraction and	638132700
Activation Tool	
Terminator Die	638405000
Mini-Mac Applicator	638916000

This document was generated on 02/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION