

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0348993120

Status:

Active

Overview:

MXP120 Sealed Connector System

Description:

MXP120 Sealed Male Blade Connector with 11.00mm Clip-Slot, 3 Circuit, Black Housing (T3-V2-S3 / T4-V4-S3), Backshell Interface Option 2, Key A

Documents:

Drawing (PDF)

Application Specification AS-34900-0001-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Application tooling part link

Application Tooling Part Link

63824-6300

General

Product Family

Series

Application

Comments

Overview

Polarization

Product Name

Taxonomy

UPC

Crimp Housings

34899

Automotive, Body Electronics, Power Train, Sealed, Wire-to-Wire

See sales drawing for terminal information.

MXP120 Sealed Connector System

A

MXP120 Sealed Connector Housings

889056519045

Physical

Circuits (maximum)

Color - Resin

Gender

Glow-Wire Capable

Keying to Mating Part

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Temperature Range - Operating

3

Black

Plug

No

Yes

Yes

SPS/Nylon

7.075/g

1

Bag

No

4.00mm

4.00mm

Yes

-40° to +125°C

Electrical

Current - Maximum per Contact

13.0A

Material Info

Reference - Drawing Numbers

Application Specification

Sales Drawing

AS-34900-0001-001

SD-34899-2001-001, SD-34899-6001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

Not Relevant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Relevant

For more information, please visit

Contact US

China ROHS

ELV

RoHS Phthalates

Not Relevant

Compliant

Not Contained

Search Parts in this Series

34899 Series

Mates With

MXP120 Female Receptacle 34900

Use With

Tyco 1.2 MCON terminals
Or
Kostal MLK 1.2 terminals

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Extraction Toolkit for MXP120 Sealed Connection System

Product #

638246300

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION