

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191930014](#)
Status: **Active**
Overview: [VersaKrimp Terminals and Splices](#)
Description: [VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire](#)

Documents:

3D Model	Product Specification PS-19902-011-001 (PDF)
Drawing (PDF)	Product Specification PS-19902-013-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	19193
Crimp Quality Equipment	Yes
Overview	VersaKrimp Terminals and Splices
Product Name	VersaKrimp
Taxonomy	Ring and Spade Terminals
Type	Ring
UPC	800755048964

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.508/g
Packaging Type	Bag
Stud Size	8 (M4)
Wire Size AWG	18, 20, 22
Wire Size mm ²	0.35-0.80

Material Info

Engineering Number	AA-321-08
--------------------	-----------

Reference - Drawing Numbers

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	191930398-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19193 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
-------------	-----------

PremiumGrade	640030100
--------------	---------------------------

Hand Crimp Tool for
Krimptite/Versakrimp
Terminals and
Splices, 10-22
AWG and 6.0mm² -
0.5mm²

Crimp Head for the	640070100
--------------------	---------------------------

AT-200 Pneumatic
Hand Tool

ServiceGrade Hand	640160038
-------------------	---------------------------

Crimp Tool - Ratchet

This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION