

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2132260410

Status:

Active

Overview:

CLIK-Mate Wire-to-Board Connectors

Description:

1.50mm Pitch CLIK-Mate Wire-to-Board PCB Receptacle, Single Row, Surface Mount, Right-Angle, 0.10µm Gold (Au) Plating, 4 Circuits, Natural

Documents:

3D Model

3D Model (PDF)


Drawing (PDF)

Product Specification 5025780004-PS-000 (PDF)

Product Specification 5025781004-PS-000 (PDF)

Packaging Specification 2132269200-SPK-200 (PDF)

RoHS Certificate of Compliance (PDF)



Series image - Reference only

General

Product Family

Series

Application

Component Type

Overview

Product Name

Taxonomy

UPC

PCB Receptacles

213226

Signal, Wire-to-Board

PCB Receptacle

CLIK-Mate Wire-to-Board Connectors

CLIK-Mate

PCB Headers and Receptacles

193264241125

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Glow-Wire Capable

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Retention

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

4

4

Natural

30

No

Yes

Yes

Yes

Copper Alloy

Gold

Polyamide

497.000/mg

1

Right Angle

No

Yes

Embossed Tape on Reel

1.50mm

1.50mm

0.102µm

0.102µm

Yes

No

No

Yes

-40° to +105°C

Surface Mount

Electrical

Current - Maximum per Contact

Voltage - Maximum

2.0A

100V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
213226 Series

Mates With
CLIK-Mate Housing 502578

Packaging Specification
Product Specification
Sales Drawing

2132269200-SPK-200
5025780004-PS-000, 5025781004-PS-000
2132260000-SD-000

This document was generated on 01/06/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION