

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192730008](#)
Status: **Active**
Overview: [Quixon Terminals](#)
Description: Quixon Quick Disconnect, Krimptite Style, Female, Un-insulated, 14-16 AWG, Loose

Documents:

Drawing (PDF)	Product Specification PS-19902-012-001 (PDF)
3D Model (PDF)	Product Specification PS-19902-013-001 (PDF)
3D Model	RoHS Certificate of Compliance (PDF)
Product Specification PS-19902-011-001 (PDF)	

Agency Certification

CSA	LR18689
UL	E79133

General

Product Family	Quick Disconnects
Series	19273
Comments	Low Insertion Force
Crimp Quality Equipment	Yes
Insulated	No
Overview	Quixon Terminals
Product Name	Krimptite, Quixon
Taxonomy	Quick Disconnects
Type	Quick Disconnect
UPC	884982564923

Physical

Barrel Type	Closed
Gender	Female
Glow-Wire Capable	No
Insulation	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.648/g
Orientation	Straight
Packaging Type	Bag
Tab Thickness	0.41mm
Tab Width	7.87mm
Temperature Range - Operating	-55° to +105°C
Wire Size AWG	14, 16

Electrical

Voltage - Maximum	Per Wire Specification
-------------------	------------------------

Material Info

Engineering Number	BB-1141-LIF
--------------------	-------------

Reference - Drawing Numbers

Product Specification	PS-19902-011-001, PS-19902-012-001, PS-19902-013-001
Sales Drawing	SD-19273-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19273 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	640031100
Crimp Head for the AT-200 Pneumatic Hand Tool	640071100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION