
This document was generated on 12/13/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 2064600041
Status: Active
Overview: Micro-Fit+ Connector System
Description: Micro-Fit+ Crimp Terminal, Female, Tin (Sn) Plating, 16 AWG



Series image - Reference only

Documents:

Drawing (PDF)
Product Specification 2064600000-PS-000 (PDF)
Application Specification 2064600001-AS-000 (PDF)
Packaging Specification 2064600000-PK-000 (PDF)
Test Summary 2064600000-TS-000 (PDF)
Datasheet (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	Crimp Terminals
Series	206460
Application	Power, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Micro-Fit+ Connector System
Product Name	Micro-Fit+
Taxonomy	Crimp Terminals
UPC	191130125456
Physical	
Durability (mating cycles max)	25
Gender	Female
Material - Metal	High Conductivity Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.092/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.00mm
Wire Size AWG	16
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	13.0A
Voltage - Maximum	600V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Application Specification	2064600001-AS-000
Packaging Specification	2064600000-PK-000
Product Specification	2064600000-PS-000
Sales Drawing	2064600000-SD-000
Test Summary	2064600000-TS-000

EU ELV
Not Relevant

EU RoHS | **China RoHS**
Compliant

REACH SVHC
Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free Status
Not Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
206460 Series

Use With
Micro-Fit Receptacle Housing 206461

Application Tooling | **FAQ**

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for Micro-Fit Terminals	11030043
FineAdjust Applicator for Micro-Fit+ Crimp Terminal, 16 AWG, UL1061 Wire	2037020800
Hand Crimp Tool for Micro-Fit Plus Crimp Terminals, 16 and 18 AWG UL1061 Wire	2133094400

Insertion Tool for Micro-Fit 3.0 and CRC Male and Female Crimp Terminals, 20-30 AWG	638120800

This document was generated on 12/13/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION