

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0353631360

Status:


Active

Overview:

Sherlock Wire-to-Board Connector System

Description:

2.00mm Pitch Sherlock Wire-to-Board Header, Right-Angle, with Positive Lock, 13 Circuits



Series image - Reference only

Documents:	
3D Model	Product Specification PS-35507-001-001 (PDF)
Drawing (PDF)	Product Specification PS-35507-003-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	35363
Application	Signal, Wire-to-Board
Component Type	PCB Header
Overview	Sherlock Wire-to-Board Connector System
Product Name	Sherlock
Taxonomy	PCB Headers and Receptacles
UPC	822348260638
Physical	
Breakaway	No
Circuits (Loaded)	13
Circuits (maximum)	13
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	0.840/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.20mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[35363](#) Series

Mates With

[35507](#) Sherlock Wire-to-Board Housing

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	125V

Material Info

Reference - Drawing Numbers

Product Specification	PS-35507-001-001, PS-35507-003-001
Sales Drawing	SD-35363-002-001, SD-35363-002-002, SD-35363-002-003

This document was generated on 01/04/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION