

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190080013

Status:

Active

Overview:

Standard Quick-Disconnect Terminals

Description:

Flag Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm²) Wire, Metal Strip, Tab 6.35 x 0.81mm

Documents:

3D Model (PDF)

Drawing (PDF)

3D Model

Product Specification PS-19902-011-001 (PDF)

Packaging Specification PK-19009-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR18689

UL

E79133

General

Product Family

Quick Disconnects

Series

19008

Crimp Quality Equipment

Yes

Insulated

No

Overview

Standard Quick-Disconnect Terminals

Product Name

Krimptite

Taxonomy

Quick Disconnects

Type

Quick Disconnect

UPC

800755046564

Physical

Barrel Type

Closed

Gender

Female

Glow-Wire Capable

No

Insulation

None

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Net Weight

0.620/g

Orientation

Flag

Packaging Type

Reel

Polarized to Mating Part

No

Tab Thickness

0.81mm

Tab Width

6.35mm

Temperature Range - Operating

Per Wire Specification

Termination Interface: Style

Crimp or Compression

Wire Size AWG

18, 20, 22

Electrical

Voltage - Maximum

Per Wire Specification

Material Info

Engineering Number

AAZ-1158

Reference - Drawing Numbers

Packaging Specification

PK-19009-001-001

Product Specification

PS-19902-011-001

Sales Drawing

5304-14, SD-19008-013-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19008 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Mini-Mac Applicator

638027500

Rear Feed

This document was generated on 02/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION