

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0351500400

Status:

Active

Overview:

VersaBlade Wire-to-Wire Connector System

Description:

VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Natural

|                                                                    |                                                                    |
|--------------------------------------------------------------------|--------------------------------------------------------------------|
| Documents:                                                         |                                                                    |
| <a href="#">3D Model (PDF)</a>                                     | <a href="#">Application Specification 351500000ASKOR-000 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                                      | <a href="#">Packaging Specification PK-35150-004-001 (PDF)</a>     |
| <a href="#">3D Model</a>                                           | <a href="#">Datasheet (PDF)</a>                                    |
| <a href="#">Product Specification PS-35150-003-001 (PDF)</a>       | <a href="#">Brochure (PDF)</a>                                     |
| <a href="#">Application Specification 351500000ASENG-000 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>               |

|                      |                                          |
|----------------------|------------------------------------------|
| Agency Certification |                                          |
| CSA                  | LR19980                                  |
| UL                   | E29179                                   |
| General              |                                          |
| Product Family       | Crimp Housings                           |
| Series               | 35150                                    |
| Application          | Power, Wire-to-Wire                      |
| Overview             | VersaBlade Wire-to-Wire Connector System |
| Product Name         | VersaBlade                               |
| Taxonomy             | Connector Housings                       |
| UPC                  | 800753876804                             |

|                               |                |
|-------------------------------|----------------|
| Physical                      |                |
| Breakaway                     | No             |
| Circuits (maximum)            | 4              |
| Color - Resin                 | Natural        |
| Flammability                  | 94V-0          |
| Gender                        | Receptacle     |
| Glow-Wire Capable             | No             |
| Keying to Mating Part         | None           |
| Lock to Mating Part           | Yes            |
| Material - Resin              | PBT            |
| Net Weight                    | 4.110/g        |
| Number of Rows                | 2              |
| Packaging Type                | Bag            |
| Panel Mount                   | No             |
| Pitch - Mating Interface      | 6.20mm         |
| Pitch - Termination Interface | 6.20mm         |
| Polarized to Mating Part      | Yes            |
| Stackable                     | No             |
| Temperature Range - Operating | -40° to +120°C |

Material Info

Reference - Drawing Numbers

|                           |                                          |
|---------------------------|------------------------------------------|
| Application Specification | 351500000AS_ENG-000, 351500000AS_KOR-000 |
| Packaging Specification   | PK-35150-004-001                         |
| Product Specification     | PS-35150-003-001                         |
| Sales Drawing             | SD-35150-0400-001                        |



Series image - Reference only

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - D(2022)4187-DC (10 June 2022)             |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Low-Halogen                                               |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series  
35150 Series

Mates With  
VersaBlade Plug Housing 35151

Use With  
VersaBlade Crimp Terminals 35745 (ckt 1), 35747 (ckt 2), 35746 (ckt 3), 35748 (ckt 4) <br>VersaBlade TPA 351500290 , 351500292 , 351500293 , 351500294

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**