

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2041020419](#)  
**Status:** **Active**  
**Overview:** [VersaBlade Wire-to-Wire Connector System](#)  
**Description:** VersaBlade Multi-Module Hybrid Plug Housing, 4 Circuits, Positive Lock, Natural, Glow-Wire Capable

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification 351500000ASKOR-000 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Packaging Specification 2041020609-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification 2041020000-000 (PDF)</a>	<a href="#">Brochure (PDF)</a>
<a href="#">Application Specification 351500000ASENG-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

UL E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">204102</a>
Application	Power, Wire-to-Wire
Overview	<a href="#">VersaBlade Wire-to-Wire Connector System</a>
Product Name	VersaBlade
Taxonomy	Connector Housings
UPC	193264280223

**Physical**

Circuits (maximum)	4
Color - Resin	Natural
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PET/PC
Net Weight	3.750/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	8.00mm, 8.50mm
Pitch - Termination Interface	8.00mm, 8.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +110°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	351500000AS_ENG-000, 351500000AS_KOR-000
Packaging Specification	2041020609-001
Product Specification	2041020000-000
Sales Drawing	2041020419-000



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[204102](#) Series

**Mates With**

VersaBlade Multi-Module 2-2 Receptacle Housing [2041020429](#) <br> VersaBlade Multi-Module 4-2 Receptacle Housing [2041020609](#)

**Use With**

VersaBlade Crimp Terminals [35746](#) (ckt 1, 2), [35745](#) (ckt 3, 4) <br> VersaBlade TPA [359650290](#) , [359650292](#) , [359650293](#) , [1040810282](#) , [495470392](#) (Upper), [495480390](#) (Lower)