

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2160101042

Status:


Active

Overview:

Super Sabre Connector System

Description:

Super Sabre-to-Super Sabre Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm Length, 4 Circuits, Black



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

|                        |                                    |
|------------------------|------------------------------------|
| General                |                                    |
| Product Family         | Cable Assemblies                   |
| Series                 | 216010                             |
| Application            | Power, Wire-to-Board, Wire-to-Wire |
| Assembly Configuration | Dual Ended Connectors              |
| Connector to Connector | Super Sabre-to-Super Sabre         |
| Overmolded             | No                                 |
| Overview               | Super Sabre Connector System       |
| Product Name           | Super Sabre                        |
| Taxonomy               | Power and Signal Cable Assembl     |
| Type                   | Discrete Wire Assembly             |
| UPC                    | 193264830398                       |

|                                |                      |
|--------------------------------|----------------------|
| Physical                       |                      |
| Cable Length                   | 300.00mm             |
| Circuits (Loaded)              | 4                    |
| Color - Resin                  | Black                |
| Gender                         | Female-Female        |
| Lock to Mating Part            | Yes                  |
| Material - Metal               | Copper               |
| Material - Plating Mating      | Silver               |
| Material - Plating Termination | Matte Tin, Nickel    |
| Material - Resin               | Nylon                |
| Net Weight                     | 83.140/g             |
| Number of Rows                 | 1                    |
| Packaging Type                 | Bag                  |
| Pitch - Mating Interface       | 7.50mm               |
| Single Ended                   | No                   |
| Termination Interface: Style   | Crimp or Compression |
| Wire Size AWG                  | 10                   |
| Wire/Cable Type                | UL 11028             |

|                               |            |
|-------------------------------|------------|
| Electrical                    |            |
| Current - Maximum per Contact | 34.0A      |
| Voltage - Maximum             | 600V AC/DC |

Material Info

|                             |                |
|-----------------------------|----------------|
| Reference - Drawing Numbers |                |
| Sales Drawing               | 2160101041-000 |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - D(2022)4187-DC (10 June 2022)             |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Low-Halogen                                                   |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

216010 Series

Mates With

Super Sabre Vertical Header [172042](#) .

Super Sabre Right Angle Header [172043](#) .

Super Sabre Plug Housing [172673](#) , [43680](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION