

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0351500209

Status:

Active

Overview:

VersaBlade Wire-to-Wire Connector System

Description:

VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 2 Circuits, Natural, Glow-Wire Capable

|                                                                    |                                                                    |
|--------------------------------------------------------------------|--------------------------------------------------------------------|
| Documents:                                                         |                                                                    |
| <a href="#">3D Model</a>                                           | <a href="#">Application Specification 351500000ASKOR-000 (PDF)</a> |
| <a href="#">3D Model (PDF)</a>                                     | <a href="#">Packaging Specification PK-35150-002-001 (PDF)</a>     |
| <a href="#">Drawing (PDF)</a>                                      | <a href="#">Datasheet (PDF)</a>                                    |
| <a href="#">Product Specification PS-35150-003-001 (PDF)</a>       | <a href="#">Brochure (PDF)</a>                                     |
| <a href="#">Application Specification 351500000ASENG-000 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>               |

|                               |                                          |
|-------------------------------|------------------------------------------|
| Agency Certification          |                                          |
| CSA                           | LR19980                                  |
| UL                            | E29179                                   |
| General                       |                                          |
| Product Family                | Crimp Housings                           |
| Series                        | 35150                                    |
| Application                   | Power, Wire-to-Wire                      |
| Overview                      | VersaBlade Wire-to-Wire Connector System |
| Product Name                  | VersaBlade                               |
| Taxonomy                      | Connector Housings                       |
| UPC                           | 756054256411                             |
| Physical                      |                                          |
| Breakaway                     | No                                       |
| Circuits (maximum)            | 2                                        |
| Color - Resin                 | Natural                                  |
| Flammability                  | 94V-0                                    |
| Gender                        | Receptacle                               |
| Glow-Wire Capable             | Yes                                      |
| Keying to Mating Part         | None                                     |
| Lock to Mating Part           | Yes                                      |
| Material - Resin              | PET/PC                                   |
| Net Weight                    | 1.706/g                                  |
| Number of Rows                | 1                                        |
| Packaging Type                | Bag                                      |
| Panel Mount                   | No                                       |
| Pitch - Mating Interface      | 6.20mm                                   |
| Pitch - Termination Interface | 6.20mm                                   |
| Polarized to Mating Part      | Yes                                      |
| Stackable                     | No                                       |
| Temperature Range - Operating | -40° to +110°C                           |
| Material Info                 |                                          |
| Reference - Drawing Numbers   |                                          |
| Application Specification     | 351500000AS_ENG-000, 351500000AS_KOR-000 |
| Packaging Specification       | PK-35150-002-001                         |
| Product Specification         | PS-35150-003-001                         |
| Sales Drawing                 | SD-35150-020X-001                        |



Series image - Reference only

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - D(2022)4187-DC (10 June 2022)             |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Low-Halogen                                               |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

35150 Series

Mates With

VersaBlade Plug Housing 35151

Use With

VersaBlade Crimp Terminals 35745  
<br>VersaBlade TPA 351500290 ,  
351500292 , 351500293 , 351500294

This document was generated on 10/20/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**