

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0731000257

Status:


Active

Overview:

SMB RF Connectors

Description:

50 Ohms, SMB Right-Angle Plug, RG-174, RG-188 and RG-316 Cable



|                                    |                                                      |
|------------------------------------|------------------------------------------------------|
| <b>Documents:</b>                  |                                                      |
| <a href="#">3D Model</a>           | <a href="#">Drawing (PDF)</a>                        |
| <a href="#">3D Model (PDF)</a>     | <a href="#">RoHS Certificate of Compliance (PDF)</a> |
| <b>General</b>                     |                                                      |
| Product Family                     | RF/Coax Connectors                                   |
| Series                             | 73404                                                |
| Overview                           | SMB RF Connectors                                    |
| Product Name                       | SMB                                                  |
| Style                              | Cable                                                |
| Taxonomy                           | RF / Coaxial Connectors                              |
| Type                               | Subminiature                                         |
| UPC                                | 800753680531                                         |
| Wire/Cable Type                    | RG-174, RG-188, RG-316                               |
| <b>Physical</b>                    |                                                      |
| Gender                             | Plug                                                 |
| Keying to Mating Part              | None                                                 |
| Net Weight                         | 2.889/g                                              |
| Orientation                        | Right Angle                                          |
| PCB Mounting                       | N/A                                                  |
| Packaging Type                     | Tray                                                 |
| Panel Mount                        | No                                                   |
| Panel Mount Method                 | N/A                                                  |
| Reverse Polar                      | No                                                   |
| <b>Electrical</b>                  |                                                      |
| Frequency                          | 4 GHz                                                |
| Impedance                          | 50Ω                                                  |
| Power / Voltage                    | VOLTAGE: 335 Vrms@Sea Level                          |
| <b>Solder Process Data</b>         |                                                      |
| Lead-freeProcess Capability        | N/A                                                  |
| <b>Material Info</b>               |                                                      |
| <b>Reference - Drawing Numbers</b> |                                                      |
| Sales Drawing                      | SD-73100-0257-001                                    |

|                                                                                                                                                                                                                                                                          |                   |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|
| <b>EU ELV</b><br><b>Not Relevant</b>                                                                                                                                                                                                                                     |                   |
| <b>EU RoHS</b><br><b>Compliant with Exemption 6(c)</b><br><b>REACH SVHC</b><br>Contained Per -<br>D(2020)9139-DC (19<br>Jan 2021)<br>Lead<br><b>Halogen-Free</b><br><b>Status</b><br><b>Low-Halogen</b><br>For more information, please visit <a href="#">Contact US</a> | <b>China RoHS</b> |
| China ROHS                                                                                                                                                                                                                                                               | 50 Image          |
| ELV                                                                                                                                                                                                                                                                      | Not Relevant      |
| RoHS Phthalates                                                                                                                                                                                                                                                          | Not Contained     |

**Search Parts in this Series**  
[73404 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION