

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0194350612](#)  
**Status:** **Active**  
**Overview:** [MX150L Industrial Sealed Connector System](#)  
**Description:** MX150L 6 Circuit Rear Mount Flange Plug for 18-22 AWG Wire, with Gasket, Black

**Documents:**  
[3D Model](#)  
[Drawing \(PDF\)](#)  
[3D Model \(PDF\)](#)  
[Product Specification PS-19417-001-001 \(PDF\)](#)  
[Packaging Specification PK-19435-001-001 \(PDF\)](#)  
[Brochure \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**  
UL E152602


**General**  
Product Family Crimp Housings  
Series [19435](#)  
Application Power, Wire-to-Wire  
Comments Mat Seal Color is Red; IP67 rated; Conforms to UL 1977; NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)  
[MX150L Industrial Sealed Connector System](#)  
Overview  
Product Name MX150L  
Taxonomy Connector Housings  
UPC 822350300407

**Physical**  
Circuits (maximum) 6  
Color - Resin Black  
Flammability 94V-0  
Gender Plug  
Glow-Wire Capable No  
Lock to Mating Part Yes  
Number of Rows 2  
Packaging Type Bag  
Panel Mount Yes  
Pitch - Mating Interface 5.84mm  
Polarized to Mating Part Yes  
Stackable No  
Temperature Range - Operating -40° to +125°C

**Electrical**  
Current - Maximum per Contact 18.0A

**Material Info**

**Reference - Drawing Numbers**  
Packaging Specification PK-19435-001-001  
Product Specification PS-19417-001-001  
Sales Drawing SD-19435-006-001



**EU ELV**  
**Not Relevant**

**EU RoHS** **China RoHS**  
**Compliant**  
**REACH SVHC**  
Contained Per -  
ED/61/2018 (27 June 2018)  
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o  
**Halogen-Free**  
**Status**  
**Low-Halogen**  
For more information, please visit [Contact US](#)  
China ROHS Green Image  
ELV Not Relevant  
RoHS Phthalates Not Reviewed

**Search Parts in this Series**  
[19435](#) Series

**Mates With**  
[19418](#) Receptacle Assemblies

**Use With**  
[19417](#) Male Crimp Terminals