

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1451300301

Status:

Active

Overview:

Nano-Fit Power Connectors

Description:

Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Cable Assembly, Single Row, Matte Tin (Sn) Plating, 150.00mm Length, 3 Circuits, Black



Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	145130
Application	Power, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Nano-Fit-to-Nano-Fit
Overmolded	No
Overview	Nano-Fit Power Connectors
Product Name	Nano-Fit
Taxonomy	Power and Signal Cable Assembl
Type	Discrete Wire Assembly
UPC	191130118823
Physical	
Cable Length	150.00mm
Circuits (Loaded)	3
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	High Conductivity Copper
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Nylon
Net Weight	5.002/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.57mm
Wire Size AWG	20
Wire/Cable Type	UL 1061
Electrical	
Current - Maximum per Contact	8.0A
Voltage - Maximum	250V AC (RMS)
Material Info	
Reference - Drawing Numbers	
Sales Drawing	4000095318-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

145130 Series

Mates With

Nano-Fit Vertical Through Hole Headers [1053091103](#) , [1053111103](#) . Nano-Fit Right-Angle Through Hole Headers [1053131103](#) . Nano-Fit Vertical SMT Headers [1054311103](#) . Nano-Fit Right-Angle SMT Headers [1054301103](#) . Nano-Fit Plug Housing [2002771103](#) , [2002771203](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION