

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0334710401

Status:

Active

Overview:

MX150 Connector System

Description:

MX150 Mat-Sealed Female Connector Assembly, Single Row, 4 Circuits, Keying Option A, Black



Series image - Reference only

Documents:	
3D Model (PDF)	Application Specification AS-33472-100-CH-001 (PDF)
3D Model	Application Specification AS-33472-100-FR-001 (PDF)
Drawing (PDF)	Application Specification AS-33611-001-001 (PDF)
Product Specification PS-33471-000-001 (PDF)	Datasheet (PDF)
Application Specification AS-33472-100-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	33471
Application	Power, Wire-to-Wire
Comments	No Connector Position Assurance (CPA)
Overview	MX150 Connector System
Product Name	MX150
Taxonomy	Connector Housings
UPC	756054458051

Physical	
Circuits (maximum)	4
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	8.765/g
Number of Rows	1
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Solder Process Data	
Lead-freeProcess Capability	N/A

Material Info

Reference - Drawing Numbers	
Application Specification	AS-33472-100-001, AS-33472-100-CH-001, AS-33472-100-FR-001, AS-33611-001-001
Product Specification	PS-33471-000-001
Sales Drawing	PK-31300-903-001

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free
Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[33471 Series](#)

Mates With
MX150 Sealed Single Row Male Connector
[33481](#)

Use With
MX150 Female Terminal [33012](#) , [33001](#)

MX150 Sealed Receptacle Cavity Plug
[343454001](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION