



REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJH 06/14/07'	~	LJC 06/14/07'
B	新增螺丝规格	YCH 11/05/11'	~	LJC 11/05/11'
C	DRAWING UPDATE	JLZ 08/08/17'	~	






RECOMMEND PCB LAYOUT(TOLERANCE  $\pm 0.05$ )  
(VIEW FROM TOP SIDE)

NOTES: 备注

- PRODUCTS PERFORMANCE:
  - VOLTAGE RATING: 250V AC.
  - CONTACT CURRENT RATING: 1.5A MAX. PER PIN.
  - CONTACT RESISTANCE: 20m $\Omega$  MAX.
  - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms) FOR 1 MINUTE.
  - INSULATION RESISTANCE: 1000M $\Omega$  MIN.
  - OPERATING TEMPERATURE: -40°C~+105°C.



- PRODUCT NUMBER CODE:  
DS1037 -01- X X X X X X X X

- SCREW DIM. E
  - 4: 4.80mm
  - 5: 5.80mm
  - ⑥: 4.80mm(Inside thread M2.6\*0.45p, outside thread unc#4-40)
  - ⑧: M3: 4.80mm(Inside thread M3.0, outside thread unc#4-40)
- BOARD LOCK DIM. F
  - 7: 3.70mm
- CONTACT PLATING
  - T: SELECTIVE GOLD FLASH
  - Si: FULL GOLD FLASH
  - 6: FULL TIN
- COLOR OF HOUSING
  - K: BLACK
  - B: BLUE
- SCREW TYPE
  - A: WITH SCREW TYPE
  - B: WITH RIVET TYPE
  - C: WITH SCREW AND RIVET TYPE
  - D: RIVET TYPE WITH SCREW IN BULD PACKAGE
- SHELL PLATING
  - N: Nickel
  - T: Tin
- CONNECTOR TYPE
  - M: MALE
  - F: FEMALE
- No. OF CONTACT
  - 09: 9pos.
  - 15: 15pos.
  - 25: 25pos.
  - 37: 37pos.






WITH SCREW TYPE

[MALE]



WITH RIVET TYPE



WITH SCREW AND RIVET TYPE

Dimension	Position	A $\pm 0.2$	B $\pm 0.2$	C $\pm 0.2$	D
	9	17.90	24.99	30.80	16.33
	15	26.50	33.32	39.14	24.66
	25	40.00	47.04	53.04	38.38
	37	56.50	63.50	69.32	54.84

GENERAL TOLERANCE	ANGLE TOLERANCE
X. $\pm 0.50$	X. $\pm 3^\circ$
.X $\pm 0.30$	.X $\pm 2^\circ$
.XX $\pm 0.20$	.XX $\pm 1^\circ$

PROJECTION	TITLE
UNITS	mm
SHEET SIZE	A4
D-SUB RIGHT ANGLE(9.4mm) TYPE	
SERIES	DS1037-01 SERIES

DRAWING TYPE	ASSEMBLY
SCALE	1:1 SHEET 1 OF 1
DRAWING NO.	C-DS1037-01-XXXXXXX-C

**晨翔电子有限公司**  
**CONNFLY CONNFLY ELECTRONIC CO. LTD**

Tel:86-574-63508787  
 Fax:86-574-63510817  
 E-mail:sale@connfly.com  
 http://www.connfly.com  
 Add: East Industry Zone KuangYan  
 Town Cixi Ningbo China  
 P.C:315333