

# SAFETY KNIFE SECUNORM PROFI25 MDP

ORDER NOW!

Order No.	120701.02
Knife size (L x W x H)	143 x 17 x 31 mm
Weight knife	84.5 g
Basic material	Aluminium
Variations	120700.02



METAL  
DETECTABLE

**18 mm cutting depth**  
for all common cutting  
materials

**Automatic blade retraction**  
for a high user protection

**Metal detectable plastic**  
for optimal detection

**Robust ergonomic handle**  
for the toughest challenges



**Smooth-running slider**  
for right and left handers

**2-cutting edge stainless steel blade**  
for a double period of use

**Abrasion resistant, uncoated  
aluminium**  
to protect against contamination  
through paint slivers (flakes)

THE SAFER WAY TO CUT.


**martor**

# MARTOR SAFETY KNIFE SECUNORM PROFIZ25 MDP

## SAFETY TECHNOLOGY



**SECUNORM**  
= high safety



### Automatic blade retraction

The automatic blade retraction of the SECUNORM PROFIZ25 MDP guarantees a high degree of safety from cut injuries. As soon as you have started to cut, take your thumb off the slider. Then the blade will retract into the handle immediately after leaving the material being cut.

## TECHNICAL FEATURES



Metal detectable



X-ray detectable



Tool-less blade change



Very abrasion resistant



Very ergonomic



2-cutting edge blade



Cutting depth



Rounded-tip trapezoid blade



For right and left handers



Stainless

## EXAMPLES OF USE



## MAIN CUTTING MATERIALS



Cardboard: up to 3-ply



Wrapping, stretch and shrink foil



Plastic strapping band



Tape



Bagged goods



Layers of foil or paper



Yarn, cord



PVC


## MOUNTABLE BLADES



**TRAPEZOID BLADE NO. 160099**

**NO. 160099.70**

0.63 mm, rounded blade tips, deep-edged, stainless, 10 in safety dispenser



**TRAPEZOID BLADE NO. 199**

**NO. 199.70**

0.63 mm, deep-edged, stainless, 10 in dispenser

## PACKING INFORMATION

<b>Packaging unit</b>	1 in single unit box (10 knives in multipack)
<b>Size Single unit box</b>	144 x 22 x 38 mm
<b>Weight single unit box</b>	99.3 g
<b>EAN Code single unit box</b>	4002632803741
<b>Size outer pack</b>	115 x 80 x 160 mm
<b>Weight outer pack</b>	1037.2 g
<b>EAN Code outer pack</b>	4002632853746