

Introducing the HyperDrive® Next 10 USB-C Hub - the ultimate connectivity solution for creators, editors, photographers, and more.

MSRP: \$99.99

SKU: HD4005GL / UPC: 817110017107



10 Ultra-fast Ports for Pro-Grade Productivity



Enhance your productivity and multitasking capabilities by providing a spacious and immersive workspace, allowing users to simultaneously view and work on multiple high-resolution content, such as videos, images, documents, and applications, with smooth and crisp visuals.



Enables lightning-fast data transfer, allowing users to move large files, backup data, and sync devices in a fraction of the time compared to traditional USB connections, increasing productivity and efficiency.



Provides high-speed and reliable wired internet connectivity, allowing for faster data transfers, seamless video streaming, and improved online gaming experiences.



Power and charge your devices up to 125W with a 140W PD 3.1 charger*, ensuring uninterrupted productivity, making it ideal for power-hungry devices and busy professionals on the go.

*When connected to PD 3.1 Host



Provides significant time savings for video editing and photography workflows, as it allows for ultra-fast and efficient transfer of high-resolution images and videos, enabling seamless editing, quicker file backups, and accelerated post-production processes.



Faster speeds and better for the planet with 100% recycled aluminium and 85% recycled plastic.

Ports Specifications:

- 4K60Hz HDMI
- 2 x USB-C 10Gbps
- USB-A 10Gbps
- USB-A 5Gbps
- microSD 312MB/s
- SD 312MB/s
- Gigabit Ethernet
- 3.5mm Audio Jack Combo
- USB-C 140W PD 3.1

Product Dimensions, Weight & Color

- Product Dims: 4.96 x 1.91 x 0.59in
0.21 lbs
- Packaged Dims: 7.32 x 4.02 x 1.38in
0.38 lbs | Qty: 1
- Color: Midnight Blue

Compatibility:

- Windows
- MacOS
- Chrome OS

Setup Specifications


- SKU: HD4005GL
- UPC: 817110017107
- EAN: 6941921149079
- Country of Origin: Vietnam
- MSRP: \$99.99

Master Carton Dimensions & Weight

- Inner Carton Dims: 14.57 x 9.06 x
4.65in | 4.6 lbs | Qty: 10
- Master Carton Dims: 15.35 x 14.96 x
10.24in | 15.3 lbs | Qty: 30

Warranty:

- Limited 2-Year Warranty



Contact Hyper sales team for more information: sales@hypershop.com

Prices, dates, features, and specifications are subject to change without notice. Many Hyper products have been granted patents. See targus.com/patents for details. ©2023 Hyper. Windows is a registered trademark of Microsoft Corporation in the United States and/or other countries. iPad and Mac are trademarks of Apple Inc., registered in the US and other countries. All trademarks and registered trademarks are the property of their respective owners.