

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191640039

Status:

Active

Overview:

Snap Plugs and Receptacles

Description:

Perma-Seal Male Snap Plug for 14-16 AWG Wire, Diameter 4.57mm

Documents:

Drawing (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E152602

General

Product Family

Quick Disconnects

Series

19164

Crimp Quality Equipment

Yes

Insulated

Partial

Overview

Snap Plugs and Receptacles

Product Name

Perma-Seal

Taxonomy

Quick Disconnects

Type

Snap Plug

UPC

800753113244

Physical

Barrel Type

Closed

Color - Resin

Blue

Gender

Male

Glow-Wire Capable

No

Insulation

NiAc

Lock to Mating Part

None

Material - Metal

Copper Alloy

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Net Weight

1.669/g

Orientation

Straight

Packaging Type

Bag

Tab Thickness

N/A

Tab Width

N/A

Temperature Range - Operating

-55° to +125°C

Wire Insulation Diameter

6.71mm max.

Wire Size AWG

14, 16

Electrical

Voltage - Maximum

600V

Material Info

Engineering Number

SB-279

Reference - Drawing Numbers

Product Specification

PS-19902-011-001, PS-19902-013-001

Sales Drawing

SD-19164-068-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19164 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade	640010300
Hand Crimp Tool for Insulkrimp Terminals and Splices, 10-22 AWG (Rings, Spades, Hooks, Block Spades and Flanged Spades)	
Crimp Head for the AT-200 Pneumatic Hand Tool	640050300

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION