

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0191640070](#)  
**Status:** **Active**  
**Overview:** [Perma-Seal Terminals](#)  
**Description:** Perma-Seal Spade Tongue Terminal for 10-12 AWG Wire, Stud Size 8 (M4)

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series [19164](#)  
 Crimp Quality Equipment Yes  
 Overview [Perma-Seal Terminals](#)  
 Product Name Perma-Seal  
 Taxonomy Ring and Spade Terminals  
 Type Spade  
 UPC 800753113541

**Physical**

Barrel Type Closed  
 Insulation NiAc  
 Material - Plating Mating Tin  
 Net Weight 1.960/g  
 Packaging Type Bag  
 Plating min - Mating 2.540µm  
 Plating min - Termination 2.540µm  
 Stud Size 8 (M4)  
 Wire Insulation Diameter 7.87mm  
 Wire Size AWG 10, 12  
 Wire Size mm<sup>2</sup> 3.09-5.01

**Material Info**

Engineering Number SC-241-08

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001, PS-19902-013-001  
 Sales Drawing SD-19164-048-001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per -  
 D(2022)4187-DC (10  
 June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[19164 Series](#)

**Application Tooling | [FAQ](#)**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

PremiumGrade [640017400](#)

Hand Crimp Tool for Industrial Terminals, 10-22 AWG (see ATS)

Power Crimp Tool [640057400](#)

Head for Terminals 10-22 AWG Wire

ServiceGrade Hand [640160041](#)

Crimp Tool for Field Repair only, for production use our PremiumGrade Tool

This document was generated on 02/01/2023

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**