

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2029361000

Status:

Active

Overview:

MultiCat Power Connectors with Precision-Machined Contacts

Description:

MultiCat Mid-Power Crimp Terminal, Female, 0.20µm Gold Plating, 20-24 AWG, without Sleeve

Documents:

- Drawing (PDF)

Product Specification 2059250000-PS-000 (PDF)

Application Specification 2059250000-AS-000 (PDF)

Packaging Specification 2029350000-PK-000 (PDF)
- Test Summary 2059250000-TS-000 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Crimp Quality Equipment

Overview

Crimp Terminals

202936

Power, Wire-to-Board, Wire-to-Wire

Yes

MultiCat Power Connectors with Precision-Machined Contacts

MultiCat

Crimp Terminals

193264027026

Physical

Durability (mating cycles max)

Gender

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Plating min - Mating

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

500

Female

Copper Alloy

Gold

Gold

0.200/g

Bag

0.200µm

Crimp or Compression

1.20-1.60mm

20, 22, 24

N/A

Electrical

Current - Maximum per Contact

Voltage - Maximum

6.5A

500V AC/DC

Material Info

Engineering Number

2029361000-FCT

Reference - Drawing Numbers

Application Specification

Packaging Specification

Product Specification

Sales Drawing

Test Summary

2059250000-AS-000

2029350000-PK-000

2059250000-PS-000

2029360000-SD-000

2059250000-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with
Exemption 6(c)

REACH SVHC

Contained Per -
D(2022)4187-DC (10
June 2022)
Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

50 Image

Not Relevant

Not Contained

Search Parts in this Series

202936 Series

Use With

MultiCat Mid-Power Receptacle Housing
205926

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for MultiCat Machined Mid-Power Contact, 20-28 AWG	2002185300
Insertion/Extraction Tool for MultiCat Mid-Power Crimp	2002220300

This document was generated on 12/29/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION