

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348993110](#)
Status: **Active**
Overview: [MXP120 Sealed Connector System](#)
Description: MXP120 Sealed Male Blade Connector with 11.00mm Clip-Slot, 3 Circuit, Yellow SIR Housing (T3-V2-S2 - 125°C on-engine vibration), Wire Dress Cover Interface Option 2, Key A

Documents:	
3D Model	Application Specification AS-34900-0001-001 (PDF)
Drawing (PDF)	Datasheet (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Application tooling part link
Application Tooling Part Link 63824-6300

General	
Product Family	Crimp Housings
Series	34899
Application	Automotive, Safety, Sealed, Wire-to-Wire
Comments	See sales drawing for terminal information.
Overview	MXP120 Sealed Connector System
Polarization	A
Product Name	MXP120 Sealed
Taxonomy	Connector Housings
UPC	889056519007

Physical	
Circuits (maximum)	3
Color - Resin	Yellow
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	4.505/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.00mm
Pitch - Termination Interface	4.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C

Electrical	
Current - Maximum per Contact	13.0A

Material Info

Reference - Drawing Numbers	
Application Specification	AS-34900-0001-001
Sales Drawing	SD-34899-2001-001, SD-34899-6001-001



Series image - Reference only

EU ELV
Compliant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2022)4187-DC (10
June 2022)
Halogen-Free
Status
Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[34899 Series](#)

Mates With
MXP120 Female Receptacle [34900](#)

Use With
Tyco 1.2 MCON terminals
Or
Kostal
MLK 1.2 terminals

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Toolkit for MXP120 Sealed Connection System	638246300

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION