

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2005280161

Status:


Active

Overview:

Easy-On FFC FPC Connectors

Description:

Easy-On FFC/FPC Connector, 1.00mm Pitch, FD19 Series, Right-Angle, Bottom Contact, 1.90mm Height, 16 Circuits, 150°C Operating Temperature, Gold over Nickel Plating



Series image - Reference only

Documents:

- | | |
|---|--|
| 3D Model | Datasheet (PDF) |
| Drawing (PDF) | Product Guide (PDF) |
| 3D Model (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification 2005280001-PS-000 (PDF) | Reference Guide (PDF) |
| Packaging Specification 2005289200-200 (PDF) | |

General

Product Family	FFC/FPC Connectors
Series	200528
Comments	Black Actuator
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
Series Name	FD19
Taxonomy	FFC / FPC Connectors
UPC	191128824927

Physical

Actuator Type	Front Flip
Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Beige
Contact Position	Bottom
Durability (mating cycles max)	20
Mated Height	1.90mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	208.898/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.051µm
Plating min - Termination	0.051µm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +150°C
Wire/Cable Type	FFC/FPC

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

Material Info

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

200528 Series

Mates With

Premo-Flex FFC Cable [15039](#)

Reference - Drawing Numbers

Packaging Specification	2005289200-200
Product Specification	2005280001-PS-000
Sales Drawing	2005280001-SD-000, 2005281001-SD-000

This document was generated on 01/25/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION