

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1727670016](#)
Status: **Active**
Overview: [Mini-Fit Family Power Connectors](#)
Description: Mini-Fit TPA2 Plug Housing, 4.20mm Pitch, Dual Row, UL 94V-0, Low-Halogen, 16 Circuits, Panel Mount

Documents:

3D Model	Packaging Specification 1727670001-PK-000 (PDF)
Drawing (PDF)	Test Summary 2029880001-TS-000 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification 2029880001-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-172718-0000-001 (PDF)	

General

Product Family	Crimp Housings
Series	172767
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	See product specification for current derating information.
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit TPA2
Taxonomy	Connector Housings
UPC	191128362894

Physical

Circuits (maximum)	16
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	5.079/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	AS-172718-0000-001
Packaging Specification	1727670001-PK-000
Product Specification	2029880001-PS-000
Sales Drawing	SD-172767-0000-000
Test Summary	2029880001-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[172767](#) Series

Mates With

Mini-Fit TPA2 Receptacle Housing [172708](#) .
Mini-Fit Jr. Receptacle Housing [5557](#)

Use With

Mini-Fit TPA2 Male Terminal [172765](#) ,
[203070](#) . Mini-Fit TPA2 Retainer [172709](#)