

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1727080010

Status:

Active

Overview:

Mini-Fit Family Power Connectors

Description:

Mini-Fit TPA2 Receptacle Housing, 4.20mm Pitch, Dual Row, UL 94V-0, Low-Halogen, 10 Circuits

- Documents:
- Drawing (PDF)

3D Model

3D Model (PDF)

Product Specification 2029880001-PS-000 (PDF)

Product Specification PS-172718-0000-001 (PDF)

Application Specification AS-172718-0000-001 (PDF)

Packaging Specification PK-172708-0000-000 (PDF)

Test Summary 1727180001-TS-000 (PDF)

Test Summary 1727180002-TS-000 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	EU-01109
General	
Product Family	Crimp Housings
Series	172708
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	See product specification for current derating information.
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit TPA2
Taxonomy	Connector Housings
UPC	889056178082
Physical	
Circuits (maximum)	10
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	2.560/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-172718-0000-001
Packaging Specification	PK-172708-0000-000
Product Specification	2029880001-PS-000, PS-172718-0000-001
Sales Drawing	SD-172708-0000-000
Test Summary	1727180001-TS-000, 1727180002-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Not Relevant

REACH SVHC

Not Contained Per -

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

172708 Series

Mates With

Mini-Fit TPA2 Plug Housing [172762](#) , [172767](#) . Mini-Fit Jr. Plug Housing [5559](#) . Mini-Fit Jr. Header [5566](#) , [5569](#) , [35318](#) , [44130](#) , [87427](#) , [172448](#) , [46991](#) , [35317](#) , [43460](#) , [87427](#) , [172447](#) , [46207](#) . Mini-Fit Sigma Sealed Plug Housing [207017](#) . Mini-Fit Jr. Test Plug [44281](#)

Use With

Mini-Fit TPA2/Sigma Female Terminal [172718](#) , [202988](#) . Pre-Crimped Lead [219670](#) , [219671](#) . Mini-Fit TPA2 Retainer [172709](#) . Mini-Fit TPA2 CPA Retainer [203603](#)

This document was generated on 10/19/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION