

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5031492400

Status:

Active

Overview:

CLIK-Mate Wire-to-Board Connectors

Description:

CLIK-Mate Plug Housing, 1.50mm Pitch, Dual Row, Positive Lock, 24 Circuits, Natural


Documents:

2D Drawing (DXF)	Product Specification 5031491001-PS-000 (PDF)
2D Drawing DXF (PDF)	Product Specification 5031491002-PS-000 (PDF)
3D Model	Product Specification 5031491003-PS-000 (PDF)
3D Model (PDF)	Product Specification 5031491004-PS-000 (PDF)
Drawing (PDF)	Product Specification PS-505406-001-001 (PDF)
Product Specification 5031490000-PS-000 (PDF)	Application Specification AS-503149-001-001 (PDF)
Product Specification 5031490001-PS-000 (PDF)	Packaging Specification SPK-503149-001-001 (PDF)
Product Specification 5031490002-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 5031491000-PS-000 (PDF)	

Agency Certification		
UL		E29179
General		
Product Family		Crimp Housings
Series		503149
Application		Signal, Wire-to-Board
Overview		CLIK-Mate Wire-to-Board Connectors
Product Name		CLIK-Mate
Taxonomy		Connector Housings
UPC		800756961705
Physical		
Circuits (maximum)		24
Color - Resin		Natural
Gender		Plug
Glow-Wire Capable		No
Keying to Mating Part		None
Lock to Mating Part		Yes
Material - Resin		PBT
Net Weight		780.000/mg
Number of Rows		2
Packaging Type		Bag
Panel Mount		No
Pitch - Mating Interface		1.50mm
Pitch - Termination Interface		1.50mm
Polarized to Mating Part		Yes
Stackable		No
Temperature Range - Operating		-40° to +105°C

Material Info

Reference - Drawing Numbers	
Application Specification	AS-503149-001-001
Packaging Specification	SPK-503149-001-001
Product Specification	5031490000-PS-000, 5031490001-PS-000, 5031490002-PS-000, 5031491000-PS-000, 5031491001-PS-000, 5031491002-PS-000, 5031491003-PS-000, 5031491004-PS-000, PS-505406-001-001
Sales Drawing	5031490000-SD-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

503149 Series

Mates With

CLIK-Mate Right Angle Receptacles [503148](#) , [213228](#) . CLIK-Mate Vertical Receptacles [503154](#) , [505406](#) , [213227](#)

Use With

CLIK-Mate Tin Terminals [502579](#) , [503429](#) . CLIK-Mate Gold Terminals [213028](#) , [213029](#) . CLIK-Mate Pre-Crimped Lead [797581011](#) , [215710](#) , [215711](#)

This document was generated on 01/09/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION