

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0351510414](#)
Status: **Active**
Overview: [VersaBlade Wire-to-Wire Connector System](#)
Description: [VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Blue](#)

Documents:

Drawing (PDF)	Application Specification 351500000ASKOR-000 (PDF)
3D Model	Packaging Specification PK-35151-005-001 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification PS-35150-003-001 (PDF)	Brochure (PDF)
Application Specification 351500000ASENG-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	35151
Application	Power, Wire-to-Wire
Overview	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
Taxonomy	Connector Housings
UPC	800754834728

Physical

Circuits (maximum)	4
Color - Resin	Blue
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	3.746/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.20mm
Pitch - Termination Interface	6.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C

Material Info

Reference - Drawing Numbers

Application Specification	351500000AS_ENG-000, 351500000AS_KOR-000
Packaging Specification	PK-35151-005-001
Product Specification	PS-35150-003-001
Sales Drawing	SD-35151-0410-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[35151](#) Series

Mates With

VersaBlade Receptacle Housing [35150](#)

VersaBlade Multi-Module 2-3-4
Receptacle Housing [35524](#) , [2026500909](#)

Use With

VersaBlade Crimp Terminals [35746](#) (ckt 1), [35748](#) (ckt 2), [35745](#) (ckt 3), [35747](#) (ckt 4)
VersaBlade TPA [351500290](#) , [351500292](#) , [351500293](#) , [351500294](#)