

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2078410004

Status:


Active

Overview:

KK Interconnect Systems

Description:

KK Plus 250 Receptacle Housing, 2.50mm Pitch, Single Row, 4 Circuits, UL 94V-0, Black, Glow-Wire Capable



Documents:	
3D Model	Product Specification 2079020001-PS-SK-000 (PDF)
3D Model (PDF)	Application Specification 2079020001-AS-000 (PDF)
Drawing (PDF)	Packaging Specification 2078410000-PK-000 (PDF)
Product Specification 2079020001-PS-000 (PDF)	Test Summary 2079020000-TS-000 (PDF)
Product Specification 2079020001-PS-CH-000 (PDF)	Datasheet (PDF)
Product Specification 2079020001-PS-ES-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 2079020001-PS-JP-000 (PDF)	

Agency Certification	
CSA	152514
UL	E29179
General	
Product Family	Crimp Housings
Series	207841
Application	Power, Wire-to-Board
Overview	KK Interconnect Systems
Product Name	KK Plus
Taxonomy	Connector Housings
UPC	191130123957
Physical	
Circuits (maximum)	4
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.341/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Material Info	
Reference - Drawing Numbers	
Application Specification	2079020001-AS-000
Packaging Specification	2078410000-PK-000
Product Specification	2079020001-PS-000, 2079020001-PS-CH-000, 2079020001-PS-ES-000, 2079020001-PS-JP-000, 2079020001-PS-SK-000
Sales Drawing	2078410004-SD-000
Test Summary	2079020000-TS-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207841 Series

Mates With

KK Plus 250 Header 207843

Use With

KK Plus 250 Crimp Terminals 46626 . KK Plus 250 TPA Retainer 207845

This document was generated on 10/12/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION