This document was generated on 02/02/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 5023800400
Status: Active
Overview: CLIK-Mate Wire-to-Board Connectors
Description: CLIK-Mate Plug Housing, 1.25mm Pitch, Single Row, Positive Lock, 4 Circuits, White



Series image - Reference only

Documents:

Drawing (PDF)
3D Model (PDF)
3D Model
Product Specification PS-502382-001-001 (PDF)
Product Specification PS-502382-002-001 (PDF)
Application Specification AS-502380-001-001 (PDF)
Application Specification AS-502380-002-001 (PDF)
Packaging Specification SPK-502380-001-001 (PDF)
Packaging Specification SPK-502380-001-002 (PDF)
RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	502380
Application	Signal, Wire-to-Board
Overview	CLIK-Mate Wire-to-Board Connectors
Product Name	CLIK-Mate
Taxonomy	Connector Housings
UPC	822350894869
Physical	
Breakaway	No
Circuits (maximum)	4
Color - Resin	White
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	149.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Electrical	
Current - Maximum per Contact	1.0A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-502380-001-001, AS-502380-002-001
Packaging Specification	SPK-502380-001-001, SPK-502380-001-002
Product Specification	PS-502382-001-001, PS-502382-002-001
Sales Drawing	SD-502380-001-001, SD-502380-001-002, SD-502380-002-001, SD-502380-002-002

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free Status
Not Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
502380 Series

Mates With
CLIK-Mate PCB Receptacle 502382 , 502386

Use With
CLIK-Mate Terminal 502381 . CLIK-Mate Pre-Crimped Leads 797581012 , 797581013

This document was generated on 02/02/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION