

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5023800200

Status:

Active

Overview:

CLIK-Mate Wire-to-Board Connectors

Description:

CLIK-Mate Plug Housing, 1.25mm Pitch, Single Row, Positive Lock, 2 Circuits, White

Documents:	
3D Model (PDF)	Application Specification AS-502380-001-001 (PDF)
Drawing (PDF)	Application Specification AS-502380-002-001 (PDF)
3D Model	Packaging Specification SPK-502380-001-001 (PDF)
Product Specification PS-502382-001-001 (PDF)	Packaging Specification SPK-502380-001-002 (PDF)
Product Specification PS-502382-002-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	502380
Application	Signal, Wire-to-Board
Overview	CLIK-Mate Wire-to-Board Connectors
Product Name	CLIK-Mate
Taxonomy	Connector Housings
UPC	822350894845

Physical	
Breakaway	No
Circuits (maximum)	2
Color - Resin	White
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	109.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Electrical	
Current - Maximum per Contact	1.0A

Material Info

Reference - Drawing Numbers	
Application Specification	AS-502380-001-001, AS-502380-002-001
Packaging Specification	SPK-502380-001-001, SPK-502380-001-002
Product Specification	PS-502382-001-001, PS-502382-002-001
Sales Drawing	SD-502380-001-001, SD-502380-001-002, SD-502380-002-001, SD-502380-002-002



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
502380 Series

Mates With
CLIK-Mate PCB Receptacle 502382 , 502386

Use With
CLIK-Mate Terminal 502381 . CLIK-Mate Pre-Crimped Leads 797581012 , 797581013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION