



PROFIBOX, 100 SCHUKO sockets and 100 SCHUKO covers with Shutters Titan White

Model	
product brand name	DELTA
product designation	SCHUKO socket outlet
design of the product	with Schuko cover
cover version	central plate
design of the special power supply unit	without special current supply
design of the socket according to VDE 0620 for severe conditions	No
design of the phase tap	No
General technical data	
marking of socket outlet	without imprint
mounting type	fixing with claw and screw
surface processing	others
material	thermoplastic
Supply voltage	
operating voltage rated value	250 V
supply voltage frequency rated value	50 Hz
Protection class	
protection class IP	IP20
Main circuit	
operational current rated value	16 A
Appearance	
color	titanium white
Product details	
product component	
<ul style="list-style-type: none"> <li>• ejection equipment</li> <li>• labeling field</li> <li>• increased touch protection</li> <li>• residual current device</li> <li>• miniature fuse</li> <li>• integrated functional lighting</li> <li>• integrated light source</li> <li>• integrated orientation lighting</li> <li>• hinged lid</li> </ul>	<ul style="list-style-type: none"> <li>No</li> <li>No</li> <li>Yes</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> <li>No</li> </ul>
product feature	
<ul style="list-style-type: none"> <li>• lockable</li> <li>• halogen-free</li> <li>• transparent</li> </ul>	<ul style="list-style-type: none"> <li>No</li> <li>Yes</li> <li>No</li> </ul>
Product function	
product function	

- socket selectable
- overvoltage protection

No  
No

#### Number

number of units	1
number of sockets switchable	0

#### Connections

arrangement of contacts diagonal	No
type of electrical connection	plug terminal

#### Mechanical Design

height	500 mm
width	400 mm
depth	200 mm
fastening method	Unterputz
material of the enclosure	plastic

#### General Product Approval

other

#### Environment



[Confirmation](#)

[Miscellaneous](#)

[Environmental Confirmations](#)

#### Further information

**Siemens has decided to exit the Russian market (see here).**

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

**Siemens is working on the renewal of the current EAC certificates.**

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

**Information on the packaging**

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5UB1518-0KA>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/5UB1518-0KA>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5UB1518-0KA](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5UB1518-0KA)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

last modified:

3/21/2023

