


Pin busbar, 10 mm<sup>2</sup> connection: 2x (1-phase+AUX/FS) touch-safe



| Model                           |                       |                           |
|---------------------------------|-----------------------|---------------------------|
| product brand name              | SENTRON               |                           |
| product designation             | Pin busbar            |                           |
| design of the product           | 10 mm², 2X(1PH+AS/FC) |                           |
| General technical data          |                       |                           |
| phase number                    | 1                     |                           |
| cross-section                   | 10 mm²                |                           |
| Main circuit                    |                       |                           |
| operational current rated value | 63 A                  |                           |
| Product details                 |                       |                           |
| product feature insulated       | Yes                   |                           |
| Connections                     |                       |                           |
| type of electrical connection   | Pin                   |                           |
| Mechanical Design               |                       |                           |
| width                           | 3.8 mm                |                           |
| length                          | 40 mm                 |                           |
| net weight                      | 7.03 g                |                           |
| General Product Approval        |                       | Declaration of Conformity |
|                                 |                       | other                     |

[Confirmation](#)

[Miscellaneous](#)



EG-Konf.

[Confirmation](#)

| other | Environment |
|-------|-------------|
|-------|-------------|

[Miscellaneous](#)

[Environmental Con-  
firmations](#)

### Further information

Siemens has decided to exit the Russian market (see here).  
<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5ST3603>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5ST3603>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5ST3603](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5ST3603)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



¹) Pin spacings in MW (Modular widths, 1 MW = 18 mm).

