



Cover for position switch for plastic enclosure 50 mm, Color yellow

product designation		cover for 50 mm wide enclosures, plastic, yellow	
General technical data			
protection class IP		IP66/IP67	
shock resistance			
• according to IEC 60068-2-27		30g / 11 ms	
vibration resistance			
• according to IEC 60068-2-6		0.35 mm/5g	
Substance Prohibitance (Date)		07/01/2006	
length of the sensor		53 mm	
width of the sensor		50 mm	
Ambient conditions			
ambient temperature			
• during operation		-25 ... +85 °C	
• during storage		-40 ... +90 °C	
explosion protection category for dust		none	
Enclosure			
design of the housing		block, wide	
coating of the enclosure		Other types	
Drive Head			
design of the actuating element		without	
cable entry type		M12 plug	
Installation/ mounting/ dimensions			
mounting position		any	
fastening method		screw fixing	
design of the interface for safety-related communication		without	
Communication/ Protocol			
design of the interface		without	
Certificates/ approvals			
General Product Approval			Functional Safety/Safety of Machinery



[Confirmation](#)



[Type Examination Certificate](#)

Declaration of Conformity	Test Certificates	other
---------------------------	-------------------	-------

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SE5240-0AA00-1AG0>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE5240-0AA00-1AG0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SE5240-0AA00-1AG0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE5240-0AA00-1AG0&lang=en



last modified:

7/14/2021