

Box terminal TS1.1 3 units 14 AWG...3/0 accessories for: 3VA4/5 125



Model	
product brand name	SENTRON
product designation	accessories
design of the product	box terminal 3 units
accessories	Box terminal
General technical data	
designation / of the terminal	TS1.1
type of electrical connection / with control wire tap	No
Connections according IEC	
connectable conductor cross-section	
• for copper cable / stranded / minimum	1.5 mm ²
• for copper cable / stranded / maximum	70 mm ²
stripped length	12 mm
tightening torque / when using copper cables	
• solid	1.5 - 16 mm ² : 45 lb-in
• stranded	1.5 - 16 mm ² : 45 lb-in 25 - 70 mm ² : 70 lb-in
• finely stranded	1.5 - 16 mm ² : 45 lb-in 25 - 50 mm ² : 70 lb-in
Connections according UL	
stripped length	0.5 in
connectable conductor cross-section	
• for copper cable / solid / minimum	14 AWG
• for copper cable / solid / maximum	10 AWG
• for copper cable / stranded / minimum	14 AWG
• for copper cable / stranded / maximum	3/0 AWG
• for copper cable / finely stranded / minimum	14 AWG
• for copper cable / finely stranded / maximum	3/0 AWG
tightening torque / when using copper cables	
• solid	14 - 10 AWG: 45 lb-in
• stranded	14 - 6 AWG: 45 lb-in 4 AWG - 3/0: 70 lb-in
• finely stranded	14 - 6 AWG: 45 lb-in 4 AWG - 3/0: 70 lb-in

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9133-0JA11>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9133-0JA11>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9133-0JA11

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

8/17/2022 

