



Part Number : [190090010](#)
Product Description : VibraKrimp Quick Disconnect Flag, Female, for 14-16 AWG Wire
Series Number : 19009
Status : Active
Product Category : Quick Disconnects
Engineering Number : BB-4169



Documents & Resources

Drawings

[Drawing 190090010_sd.pdf](#)

3D Models and Design Files

[3D Model 190090010_stp.zip](#)

Specifications

[Product Specification PS-19902-005-001.pdf](#)

[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19009
Description	VibraKrimp Quick Disconnect Flag, Female, for 14-16 AWG Wire
Comments	Wire Grip
Product Family	Standard Quick-Disconnect Terminals
Product Name	VibraKrimp
Type	Quick Disconnect
UPC	800755046885

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	Per Wire Specification
-------------------	------------------------

Physical

Barrel Type	Closed
Gender	Female
Glow-Wire Capable	No
Insulated	No
Insulation	None

Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.764/g
Orientation	Flag
Packaging Type	Bag
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	Per Wire Specification
Wire Insulation Diameter	3.68mm
Wire Size (AWG)	14, 16
Wire Size mm ²	1.30-2.00

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Flag Krimptite/Vibrakrimp Un-insulated Female Quick Disconnect Terminals, 14-22 AWG	<u>0640034200</u>